



26-2000 Series

26-2000 Series High Pressure Reducing



Spring Loaded



All dimensions are reference & nominal
Metric (millimeter) equivalents are in brackets





Dome Loaded



INLET & OUTLET PORT	'A'
ALL 1/4 EXCEPT NPT	2.30
1/4 NPT	Ø2.48
3/8 NPT	Ø2.48
ALL 3/8 EXCEPT NPT	2.90
1/2 MS33649	2.90
1/2 NPT	Ø3.20

Air Loaded





26-2000 Series High Pressure Reducing

Part Number Selector

example part number:

26-20 **6** **1** **A** **2** **4** **S** **1** **7** **0**

BASIC SERIES	BODY MATERIAL	MAXIMUM INLET PRESSURE	OUTLET PRESSURE (PSIG)	SOFT GOODS MATERIAL			IN & OUT PORT TYPE	VENT PORT	INLET & OUTLET PORT SIZE	FLOW CAPACITY (C _v)	MAIN VALVE SEAT & VENT SEAT MATERIAL	GAUGE PORT OPTIONS
				O-RING		back-up ring						
				dynamic	static							
26-20	1 – Brass	6,000 PSIG	Spring Load	A – Teflon®	Viton®	Teflon®	1 – SAE	1/4" SAE	4 – 1/4" 6 – 3/8" 8 – 1/2" **	1 – .02 <i>(not available for metal seated models)</i> 2 – .06 3 – .12 *** <i>(metal and/or Vespe!® seat only)</i>	5 – 17-4 SST 7 – Vespe!® 8 – Peek	0 – None  1 – One Outlet Gauge @ 90°  2 – Two Gauge Ports @ 60°  3 – Two Gauge Ports @ 60° (left hand inlet)  4 – Two Gauge Ports @ 90°  5 – One Outlet Gauge @ 90° (left hand inlet) 
	6 – 316 SST	10,000 PSIG		B – Buna-N 90	Buna-N 90	Teflon®	2 – NPT	1/4" NPT				
	9 – 316 SST	15,000 PSIG* <i>(spring & air load only)</i>		D – Buna-N	Buna-N	Teflon®	3 – MS33649	1/4" MS33649				
				J – Teflon®	Viton®	Teflon®	4 – High Pressure	1/4" NPT				
				N – Neoprene	Neoprene	Teflon®	6 – Medium Pressure	1/4" NPT				
				T – Viton®	Viton®	Teflon®						
				U – Urethane	Urethane	Teflon®						
				V – Kalrez®	Kalrez®	Teflon®						
				Z – E.P.	E.P.	Teflon®						
				Dome Load								
					1 – 200-10,000 <i>(SST body only)</i>							
					2 – 50-6000							
			Air Load									
				1 – 200-10,000 <i>(SST body only)</i>								
				2 – 50-6000								
				4 – 15-2500								
			5 – 10-1500									

* 15,000 PSIG inlet requires a CTFE back-up ring on main valve, consult Tescom.

** Not available in High or Medium pressure.

*** Not available with 15,000 PSIG inlet.

* 15,000 PSIG inlet requires a CTFE back-up ring on main valve, consult Tescom.

** Not available in High or Medium pressure.


*** Not available with 15,000 PSIG inlet.

Repair Kits, Accessories & Modifications may be available for this product. Please contact factory for more information.

Flow Charts


Dome and air loaded flow charts on reverse side

Spring Loaded




26-2000 Series High Pressure Reducing Flow Charts

Dome Loaded



Air Loaded



WARNING! Do not attempt to select, install, use or maintain this product until you have read and fully understood the *Tescom Safety, Installation & Operation Precautions*.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. We reserve the right to modify or improve the designs or specifications of such product at any time without notice.

For information contact:

TESCOM
www.TESCOM.com

TESCOM Industrial Controls
Tel: 800-447-1250 • 763-241-3238
Fax: 763-241-3224 • email: ic@tescom.com
12616 Industrial Boulevard • Elk River, MN 55330 USA

©Tescom Corporation, 2006; All Rights Reserved.
Tescom is a business unit of the Regulator Division.
Trademarks are property of divisions of Emerson Process Management.

Form No. 1821 Rev. 4/06 Printed 4/06 5M Printed in the U.S.A.



EMERSON
Process Management